



# GP Flood Series - GP5

## GP5S1000LXL-8

HPS, 1000W, 120-277V, w/Lamp, Slipfitter, Flood

The GP5 Flood Series combines architectural design with on-site versatility and is designed for general purpose floodlighting installations. Applications include security, roadway, area, accent, facade, recreational fields, flagpole, and sign lighting. The GP5 Flood series is available with BT56 lamps for metal halide and E25 lamps for high pressure sodium up to 1500 watts. Reflectors include general purpose, spot and cut-off optics for control of light trespass. IP65 Rated for extra protection against water, dust and debris, and can be aimed above or below horizontal. The GP 5 is also available in a 165W very-long life induction sources for 100,000 hours.

### Product data

General Information	
Lamp Source Code	High Pressure Sodium
Lamp Watts	1000
Number of Lamps	1
Photometric Distribution Type	Flood
Mounting	Ground / Floor
Operating and Electrical	
Voltages	120/277 V
Maximum Lamp Watts	1000
Product Data	
Order product name	GP5S1000LXL-8

EAN/UPC - Product	190096002726
Order code	GP5S1000LXL-8
Local order code	-
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400480772
Net Weight (Piece)	27215.520 g
Commercial Code	GP5S1000LXL-8
Catalog Number Description	HPS, 1000W, 120-277V, w/Lamp, Slipfitter, Flood
Quick Ship	-