



# GP Flood Series - GP4

## FLOOD, GP4, SLIPFITTER, 250W, HPS WITH L

HPS, 250W, 120-277V, w/Lamp, Slipfitter, Flood

The GP4 Flood Series combines architectural design with on-site versatility and is designed for general purpose floodlighting installations. Applications include security, roadway, area, accent, facade, recreational fields, flagpole, and sign lighting. The GP4 Flood series is available with ED28 lamps for pulse start metal halide and ED18 lamps for high pressure sodium up to 400 watts. Reflectors include general purpose, spot and cut-off optics for control of light trespass. IP65 Rated for extra protection against water, dust and debris, and can be aimed above or below horizontal. The GP4 is also available in 55W and 85W very-long life induction sources for 100,000 hours.

### Product data

General Information		EAN/UPC - Product	
Lamp Source Code	High Pressure Sodium	Order code	GP4S250LXL-8
Lamp Watts	250	Local order code	.
Number of Lamps	1	Numerator - Quantity Per Pack	1
Photometric Distribution Type	Flood	Numerator - Packs per outer box	1
Mounting	Ground / Floor	Material Nr. (12NC)	912400518335
Operating and Electrical		Net Weight (Piece)	0.010 kg
Voltages	120/208/240/277 V	Commercial Code	GP4S250LXL-8
Maximum Lamp Watts	250	Catalog Number Description	HPS, 250W, 120-277V, w/Lamp, Slipfitter, Flood
Product Data		Quick Ship	-
Order product name	FLOOD, GP4, SLIPFITTER, 250W, HPS WITH L		