



# GP Flood Series - GP4

## GP4T250LXL-8

HPS, 250W, 120-277V, w/Lamp, Trunnion, Flood

The GP4 Flood Series combines architectural design with on-site versatility and is designed for general purpose floodlighting installations. Applications include security, roadway, area, accent, facade, recreational fields, flagpole, and sign lighting. The GP4 Flood series is available with ED28 lamps for pulse start metal halide and ED18 lamps for high pressure sodium up to 400 watts. Reflectors include general purpose, spot and cut-off optics for control of light trespass. IP65 Rated for extra protection against water, dust and debris, and can be aimed above or below horizontal. The GP4 is also available in 55W and 85W very-long life induction sources for 100,000 hours.

### Product data

<b>General Information</b>		<b>Order code</b>	GP4T250LXL-8
<b>Lamp Source Code</b>	High Pressure Sodium	<b>Local order code</b>	.
<b>Lamp Watts</b>	250	<b>Numerator - Quantity Per Pack</b>	1
<b>Number of Lamps</b>	1	<b>Numerator - Packs per outer box</b>	1
<b>Photometric Distribution Type</b>	Flood	<b>Material Nr. (12NC)</b>	912400531067
<b>Mounting</b>	Ground / Floor	<b>Net Weight (Piece)</b>	0.200 kg
<b>Operating and Electrical</b>		<b>Commercial Code</b>	GP4T250LXL-8
<b>Voltages</b>	120/208/240/277 V	<b>Catalog Number Description</b>	HPS, 250W, 120-277V, w/Lamp, Trunnion, Flood
<b>Maximum Lamp Watts</b>	250	<b>Quick Ship</b>	-
<b>Product Data</b>			
<b>Order product name</b>	GP4T250LXL-8		