



# GP Flood Series - GP4

**HPS, 250W, 120-277V, Cutoff Optics, w/Lamp, Trunnion, Flood**

HPS, 250W, 120-277V, Cutoff Optics, w/Lamp, Trunnion, Flood

The GP4 Flood Series combines architectural design with on-site versatility and is designed for general purpose floodlighting installations. Applications include security, roadway, area, accent, facade, recreational fields, flagpole, and sign lighting. The GP4 Flood series is available with ED28 lamps for pulse start metal halide and ED18 lamps for high pressure sodium up to 400 watts. Reflectors include general purpose, spot and cut-off optics for control of light trespass. IP65 Rated for extra protection against water, dust and debris, and can be aimed above or below horizontal. The GP4 is also available in 55W and 85W very-long life induction sources for 100,000 hours.

## Product data

<b>General Information</b>		<b>Order code</b> GP4T250LXLC-8	
Lamp Source Code	High Pressure Sodium	Numerator - Quantity Per Pack	1
Lamp Watts	250	Numerator - Packs per outer box	1
Number of Lamps	1	Material Nr. (12NC)	912400531074
Photometric Distribution Type	NEMA 6H x 5V	Net Weight (Piece)	0.200 kg
Mounting	Ground / Floor	Catalog Number	GP4T250LXLC-8
<b>Operating and Electrical</b>		Catalog Number Description	HPS, 250W, 120-277V, Cutoff Optics, w/Lamp, Trunnion, Flood
Voltages	120/208/240/277 V		
Maximum Lamp Watts	250		
<b>Product Data</b>			
Order product name	GP4T250LXLC-8		