



# 60 Series Exits

## 60MLA1RWA

Wet Location/Vandal Resistant LED Exit, AC Only, Single Face, Red Letters, White Housing and Brushed Aluminum Stencil

The 60 Line Max is designed to meet the demands of todays most extreme environments. An attractive housing constructed of durable die cast with a polycarbonate backplate and cover. Built for extreme temperatures and vandalproof applications.

### Product data

<b>General Information</b>		<b>Local order code</b>	
Lamp Source Code	LED	Numerator - Quantity Per Pack	1
Mounting	Wall Suspended	Numerator - Packs per outer box	1
<b>Operating and Electrical</b>		Material Nr. (12NC)	912401045911
Voltages	120/277 V	Net Weight (Piece)	0.100 kg
Luminaire Input Watts	4	Commercial Code	60MLA1RWA
<b>Product Data</b>		Catalog Number Description	Wet Location/Vandal Resistant LED Exit, AC Only, Single Face, Red Letters, White Housing and Brushed Aluminum Stencil
Order product name	60MLA1RWA	Quick Ship	-
EAN/UPC - Product	781370995324		
Order code	912401045911		