



60 Series Exits

60MLA1GB

Wet Location/Vandal Resistant LED Exit, AC Only, Single Face, Green Letters, Black Housing and Black Stencil

The 60 Line Max is designed to meet the demands of todays most extreme environments. An attractive housing constructed of durable die cast with a polycarbonate backplate and cover. Built for extreme temperatures and vandalproof applications.

Product data

General Information		Local order code	
Lamp Source Code	LED	Numerator - Quantity Per Pack	1
Mounting	Wall Suspended	Numerator - Packs per outer box	1
Operating and Electrical		Material Nr. (12NC)	912401045914
Voltages	120/277 V	Net Weight (Piece)	0.100 kg
Luminaire Input Watts	4	Commercial Code	60MLA1GB
Product Data		Catalog Number Description	Wet Location/Vandal Resistant LED Exit, AC Only, Single Face, Green Letters, Black Housing and Black Stencil
Order product name	60MLA1GB	Quick Ship	-
EAN/UPC - Product	781370995362		
Order code	912401045914		