



# Wal-Lyter LED Recessed Wall Wash

WLRN17L835-2-UNV

LED Recessed Wall Wash, 2'

The Philips Day-Brite / Philips CFI Wal-Lyter LED Recessed Wallwash is a high performance luminaire luminaire that delivers good light levels and an even wash of light. Low-iridescent semi-specular reflectors do not protrude below the ceiling line. This provides a clean appearance while controlling the light output of high efficiency LED boards to illuminate vertical surfaces uniformly.

## Product data

General Information	
Lamp Source Code	LED
Colour Temperature	3500K
CRI	80
Photometric Distribution Type	Direct
Mounting	Recessed franse vertaling T-Bar / T-Grid
Operating and Electrical	
Voltages	120/277/UNIV V
Luminaire Input Watts	32
Mechanical and Housing	
Fixture Size	1 ft x 2 ft
Shape	Rectangular
Initial Performance (IEC Compliant)	
Luminaire Lumens	1736

Product Data	
Order product name	WLRN17L835-2-UNV
EAN/UPC - Product	781370207007
Order code	912401260250
Local order code	-
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912401260250
Net Weight (Piece)	0.001 kg
Commercial Code	WLRN17L835-2-UNV
Catalog Number Description	LED Recessed Wall Wash, 2'
Quick Ship	-

## Wal-Lyter LED Recessed Wall Wash

