



Wal-Lyter LED Recessed Wall Wash

WLRN35L835-4-UNV

LED Recessed Wall Wash, 4'

The Philips Day-Brite / Philips CFI Wal-Lyter LED Recessed Wallwash is a high performance luminaire luminaire that delivers good light levels and an even wash of light. Low-iridescent semi-specular reflectors do not protrude below the ceiling line. This provides a clean appearance while controlling the light output of high efficiency LED boards to illuminate vertical surfaces uniformly.

Product data

General Information	
Lamp Source Code	LED
Color Temperature	3500K
CRI	80
Photometric Distribution Type	Direct
Mounting	Recessed T-Bar / T-Grid
Operating and Electrical	
Voltages	120/277/UNIV V
Luminaire Input Watts	53
Mechanical and Housing	
Fixture Size	1 ft x 4 ft
Shape	Rectangular
Initial Performance (IEC Compliant)	
Luminaire Lumens	3565

Product Data	
Order product name	WLRN35L835-4-UNV
EAN/UPC - Product	781370207281
Order code	912401260251
Local order code	7020728
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912401260251
Net Weight (Piece)	0.001 kg
Commercial Code	WLRN35L835-4-UNV
Catalog Number Description	LED Recessed Wall Wash, 4'
Quick Ship	-

Wal-Lyter LED Recessed Wall Wash

