



Wal-Lyter LED Recessed Wall Wash

LED Recessed Wall Wash, 4'

LED Recessed Wall Wash, 4'

The Day-Brite / CFI Wal-Lyter LED Recessed Wallwash is a high performance luminaire luminaire that delivers good light levels and an even wash of light. Low-iridescent semi-specular reflectors do not protrude below the ceiling line. This provides a clean appearance while controlling the light output of high efficiency LED boards to illuminate vertical surfaces uniformly.

Product data

General Information		Initial Performance (IEC Compliant)	
Lamp Source Code	LED	Luminaire Lumens	3565
Colour Temperature	3500K		
CRI	80	Product Data	
Photometric Distribution Type	Direct	Order product name	WLRN35L835-4-UNV
Mounting	Recessed T-Bar / T-Grid	EAN/UPC - Product	781370207281
		Order code	WLRN35L835-4-UNV
		Numerator - Quantity Per Pack	1
		Numerator - Packs per outer box	1
		Material Nr. (12NC)	912401260251
		Net Weight (Piece)	0.001 kg
		Catalog Number	WLRN35L835-4-UNV
		Catalog Number Description	LED Recessed Wall Wash, 4'
Operating and Electrical			
Voltages	120/277/UNIV V		
Luminaire Input Watts	53		
Mechanical and Housing			
Fixture Size	1 ft x 4 ft		
Shape	Rectangular		