



Arioso Recessed LED

2AVEG38L835-2-ACR-UNV

2x2, 3800 Nominal Delivered Lumens, 3500K, Frosted Acrylic Lens - 95 lm/W

The Philips Day-Brite / Philips CFI Arioso Recessed LED offers standard-setting efficiency without aesthetic compromise. These LED luminaires combine state-of-the-art, flexible and globally- recognized LED lighting platforms with proven Arioso optical combinations.

Product data

General Information		Efficacy 95 lm/W	
Lamp Source Code	LED		
Color Temperature	3500K		
CRI	80		
Photometric Distribution Type	Direct		
Mounting	Recessed		
Operating and Electrical		Product Data	
Voltages	UNIV V	Order product name	2AVEG38L835-2-ACR-UNV
Luminaire Input Watts	40	EAN/UPC - Product	781370296926
		Order code	912401260941
		Local order code	7029692
		Numerator - Quantity Per Pack	1
		Numerator - Packs per outer box	1
		Material Nr. (12NC)	912401260941
		Net Weight (Piece)	0.001 kg
		Commercial Code	2AVEG38L835-2-ACR-UNV
		Catalog Number Description	2x2, 3800 Nominal Delivered Lumens, 3500K, Frosted Acrylic Lens
		Quick Ship	-
Mechanical and Housing			
Fixture Size	2 ft x 2 ft		
Shape	Square		
Initial Performance (IEC Compliant)			
Luminaire Lumens	3800		