



DuaLED Recessed

1x4, 3600 Nominal Delivered Lumens, 3500K, Diffuse

1x4, 3600 Nominal Delivered Lumens, 3500K, Diffuse - 95 lm/W

DuaLED was thoughtfully developed as a sustainable luminaire with a modern appearance and uncomplicated design, also offering exceptional quality and performance, for an outstanding benefit to the customer. DuaLED is a highly efficient, architecturally styled recessed LED luminaire designed with a minimalistic strategy to achieve sustainable objectives. It combines an extremely low profile with clean aesthetics and is powered by highly efficient advanced LED sources, providing the utmost in comfortable efficient lighting. Driver and integral control options ensure optimization for every application. Designed for excellent visual comfort, DuaLED is perfect for a wide variety of general applications like offices, schools, retail, or healthcare.

Product data

General Information		Shape	
Lamp Source Code	LED	Rectangular	
Colour Temperature	3500K	Initial Performance (IEC Compliant)	
CRI	80	Luminaire Lumens	3600
Photometric Distribution Type	Direct	Efficacy	95 lm/W
Mounting	Recessed	Product Data	
Operating and Electrical		Order product name	1DLG36L835-4-D-UNV
Voltages	120/277/347 V	EAN/UPC - Product	782343649145
Luminaire Input Watts	38	Order code	1DLG36L835-4-D-UNV-DIM
Mechanical and Housing		Numerator - Quantity Per Pack	1
Fixture Size	1 ft x 4 ft	Numerator - Packs per outer box	1
		Material Nr. (12NC)	912401261294

DuaLED Recessed

Net Weight (Piece)	0.001 kg
Catalog Number	1DLG36L835-4-D-UNV-DIM
Catalog Number Description	1x4, 3600 Nominal Delivered Lumens, 3500K, Diffuse

