



# DuaLED Surface LED

## 1SDL36L835-4-D-UNV

1x4, 3600 Nominal Delivered Lumens, 3500K, Diffuse, Surface Mount - 95 lm/W

Surface DuaLED was thoughtfully developed as a sustainable luminaire with a modern appearance and uncomplicated design, also offering exceptional quality and performance, for an outstanding benefit to the customer. DuaLED is a highly efficient, architecturally styled recessed LED luminaire designed with a minimalistic strategy to achieve sustainable objectives. It combines an extremely low profile with clean aesthetics and is powered by highly efficient advanced LED sources, providing the utmost in comfortable efficient lighting. Driver and integral control options ensure optimization for every application. Designed for excellent visual comfort, DuaLED is perfect for a wide variety of general applications like offices, schools, retail, or healthcare. Optional SpaceWise automated wireless technology provides integrated occupancy and daylight harvesting for additional control and energy savings with no reduction of life.

### Product data

General Information	
Lamp Source Code	LED
Color Temperature	3500K
CRI	80
Photometric Distribution Type	Direct
Mounting	Surface
Operating and Electrical	
Voltages	120/277/347 V
Luminaire Input Watts	38

Mechanical and Housing	
Fixture Size	1 ft x 4 ft
Shape	Rectangular
Initial Performance (IEC Compliant)	
Luminaire Lumens	3600
Efficacy	95 lm/W
Product Data	
Order product name	1SDL36L835-4-D-UNV
EAN/UPC - Product	782343173091
Order code	912401266018

## DuaLED Surface LED

<b>Local order code</b>	4317309
<b>Numerator - Quantity Per Pack</b>	1
<b>Numerator - Packs per outer box</b>	1
<b>Material Nr. (12NC)</b>	912401266018
<b>Net Weight (Piece)</b>	0.001 kg
<b>Commercial Code</b>	1SDL36L835-4-D-UNV-DIM

<b>Catalog Number Description</b>	1x4, 3600 Nominal Delivered Lumens, 3500K, Diffuse, Surface Mount
<b>Quick Ship</b>	-

