



LSW Wall LED

Ceiling Or Wall Mounted Fluorescent, 6" Width, 3 7/8" Deep, 4000 nominal lumens, 4000K color temperature

Ceiling Or Wall Mounted Fluorescent, 6" Width, 3 7/8" Deep, 4000 nominal lumens, 4000K color temperature - 89 lm/W

LSW Lens Wrap Ceiling/Wall Mounted - Specification Grade For ceiling or wall (vertically or horizontally) mounted applications. Only 3 7/8" deep, meets Americans with Disabilities Act (wall mounted). Low brightness .125 thick linear prismatic virgin acrylic refractor. Invisible spring steel latches align refractor to housing. 20 gauge cold rolled steel post painted baked white enamel end caps. For over mirror, over bed, corridor, stairwell and bulletin board applications.

Product data

General Information	
Lamp Source Code	LED
Colour Temperature	4000K
CRI	80
Photometric Distribution Type	Direct
Mounting	Wall Surface
Operating and Electrical	
Voltages	120/277/347/UNIV V
Luminaire Input Watts	45
Mechanical and Housing	
Fixture Size	48 in

Initial Performance (IEC Compliant)	
Luminaire Lumens	4000
Efficacy	89 lm/W
Product Data	
Order product name	LS4R40A40U
EAN/UPC - Product	781370294946
Order code	LS4R40A40UDZT
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912401267051
Net Weight (Piece)	0.001 kg
Catalog Number	LS4R40A40UDZT

LSW Wall LED

Catalog Number	Description
	Ceiling Or Wall Mounted Fluorescent, 6" Width, 3 7/8" Deep, 4000 nominal lumens, 4000K color temperature

