



# DuaLED Surface LED

## 2x4, 4900 Nominal Delivered Lumens, 3500K, Diffuse, Surface Mount

2x4, 4900 Nominal Delivered Lumens, 3500K, Diffuse, Surface Mount - 102 lm/W

Surface DuaLED was thoughtfully developed as a sustainable luminaire with a modern appearance and uncomplicated design, also offering exceptional quality and performance, for an outstanding benefit to the customer. DuaLED is a highly efficient, architecturally styled recessed LED luminaire designed with a minimalistic strategy to achieve sustainable objectives. It combines an extremely low profile with clean aesthetics and is powered by highly efficient advanced LED sources, providing the utmost in comfortable efficient lighting. Driver and integral control options ensure optimization for every application. Designed for excellent visual comfort, DuaLED is perfect for a wide variety of general applications like offices, schools, retail, or healthcare. Optional SpaceWise automated wireless technology provides integrated occupancy and daylight harvesting for additional control and energy savings with no reduction of life.

### Product data

General Information		Luminaire Input Watts	
Lamp Source Code	LED		48
Colour Temperature	3500K	Mechanical and Housing	
CRI	80	Fixture Size	2 ft x 4 ft
Photometric Distribution Type	Direct	Shape	Rectangular
Mounting	Surface	Initial Performance (IEC Compliant)	
Operating and Electrical		Luminaire Lumens	4900
Voltages	120/277/347 V	Efficacy	102 lm/W

## DuaLED Surface LED

### Product Data

Order product name	2SDL49L835-4-D-UNV
EAN/UPC - Product	784197031169
Order code	2SDL49L835-4-D-UNV-DIM
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912401270552

Net Weight (Piece)	0.001 kg
Catalog Number	2SDL49L835-4-D-UNV-DIM
Catalog Number Description	2x4, 4900 Nominal Delivered Lumens, 3500K, Diffuse, Surface Mount

