



# FBX LED High Bay

## FBX20LL40-UNV

20,000 Nominal Delivered Lumens, 4000K, 80 CRI, Wide Distribution, Frosted Acrylic Lens - 124 lm/W

The FBX LED High Bay is a compact and economical luminaire utilizing the latest in LED technology. With several lumen packages and optical distribution patterns available, the FBX offers exceptional lighting in mid to high ceiling applications. Save energy without straining your project budget or sacrificing your light output.

### Product data

| General Information           |           |
|-------------------------------|-----------|
| Color Temperature             | 4000K     |
| CRI                           | 80        |
| Photometric Distribution Type | Direct    |
| Mounting                      | Suspended |

  

| Operating and Electrical |                                |
|--------------------------|--------------------------------|
| Voltages                 | 120/208/240/277/347/480/UNIV V |
| Luminaire Input Watts    | 142                            |

  

| Mechanical and Housing |       |
|------------------------|-------|
| Fixture Size           | 24 in |

  

| Initial Performance (IEC Compliant) |          |
|-------------------------------------|----------|
| Luminaire Lumens                    | 20000    |
| Efficacy                            | 124 lm/W |

| Product Data                    |   |
|---------------------------------|---|
| Order product name              | FBX20LL40-UNV   |
| EAN/UPC - Product               | 784197039073  |
| Order code                      | 912401271083  |
| Local order code                | 9703907   |
| Numerator - Quantity Per Pack   | 1   |
| Numerator - Packs per outer box | 1   |
| Material Nr. (12NC)             | 912401271083  |
| Net Weight (Piece)              | 0.001 kg  |
| Commercial Code                 | FBX20LL40-UNV-W-LFA   |
| Catalog Number Description      | 20,000 Nominal Delivered Lumens, 4000K, 80 CRI, Wide Distribution, Frosted Acrylic Lens |