



SofTrace Surface LED

2SST50L840-4-D-UNV

2x4, Surface, 5000 Nominal Delivered Lumens, 80 CRI, 4000K, Diffuse-Ribbed

SofTrace Surface LED brings new meaning to the concept of combining style with performance. Equipped with a fresh streamlined design and innovative technology, SofTrace provides a huge step forward for the lighting industry. The sleek profile design belies the true “horsepower under the hood”. With efficiency levels exceeding 95% and lumens per Watt as great as 87, an architectural product now delivers leading edge performance for the most environmentally conscious user.

Product data

| General Information | |
|-------------------------------------|---------------|
| Lamp Source Code | LED |
| Color Temperature | 4000K |
| CRI | 80 |
| Photometric Distribution Type | Direct |
| Mounting | Surface |
| Operating and Electrical | |
| Voltages | 120/277/347 V |
| Luminaire Input Watts | 49 |
| Mechanical and Housing | |
| Fixture Size | 2 ft x 4 ft |
| Shape | Rectangular |
| Initial Performance (IEC Compliant) | |
| Luminaire Lumens | 5000 |

| Product Data | |
|---------------------------------|--|
| Order product name | 2SST50L840-4-D-UNV |
| EAN/UPC - Product | 784197066901 |
| Order code | 912401272934 |
| Local order code | 9706690 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 1 |
| Material Nr. (12NC) | 912401272934 |
| Net Weight (Piece) | 0.001 kg |
| Commercial Code | 2SST50L840-4-D-UNV-DIM |
| Catalog Number Description | 2x4, Surface, 5000 Nominal Delivered Lumens, 80 CRI, 4000K, Diffuse-Ribbed |
| Quick Ship | - |

SofTrace Surface LED

