



SofTrace Air LED

2STGA38L840-2-PMW-UNV

2x2, Air Handling, 3800 Nominal Delivered Lumens, 80 CRI, 4000K,
Round Perf. w/White Overlay

SofTrace Air LED brings new meaning to the concept of combining style with performance. Equipped with a fresh streamlined design and innovative technology, SofTrace provides a huge step forward for the lighting industry. The sleek profile design belies the true “horsepower under the hood”. With efficiency levels exceeding 95% and lumens per Watt as great as 87, an architectural product now delivers leading edge performance for the most environmentally conscious user.

Product data

General Information	
Lamp Source Code	LED
Color Temperature	4000K
CRI	80
Photometric Distribution Type	Direct
Mounting	Recessed
Operating and Electrical	
Voltages	120/277/347 V
Luminaire Input Watts	45
Mechanical and Housing	
Fixture Size	2 ft x 2 ft
Initial Performance (IEC Compliant)	
Luminaire Lumens	3800

Product Data	
Order product name	2STGA38L840-2-PMW-UNV
EAN/UPC - Product	784197188108
Order code	912401278765
Local order code	9718810
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912401278765
Net Weight (Piece)	0.001 kg
Commercial Code	2STGA38L840-2-PMW-UNV-DIM
Catalog Number Description	2x2, Air Handling, 3800 Nominal Delivered Lumens, 80 CRI, 4000K, Round Perf. w/White Overlay
Quick Ship	-