



EvoGrid Recessed LED

1EVG30L840-4-D-UNV

1x4, 3000 Nominal Delivered Lumens, 80 CRI, 4000K, Diffuse - 120 lm/W

EvoGrid Recessed Architectural LED provides general lighting perfect for a wide variety of applications. Its soft opal diffuser with large luminous area minimizes apparent brightness compared to other based luminaires.

Product data

General Information	
Color Temperature	4000K
CRI	80
Photometric Distribution Type	Direct
Mounting	Recessed
Operating and Electrical	
Voltages	120/277/347/UNIV V
Luminaire Input Watts	25
Mechanical and Housing	
Fixture Size	1 ft x 4 ft
Shape	Rectangular
Approval and Application	
DesignLights Consortium Qualified Product List DesignLights Consortium Qualified Product List	
Initial Performance (IEC Compliant)	
Luminaire Lumens	3000

Efficacy	120 lm/W
Product Data	
Order product name	1EVG30L840-4-D-UNV
EAN/UPC - Product	784197333768
Order code	912401278770
Local order code	9733376
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912401278770
Net Weight (Piece)	0.001 kg
Commercial Code	1EVG30L840-4-D-UNV-DIM
Catalog Number Description	1x4, 3000 Nominal Delivered Lumens, 80 CRI, 4000K, Diffuse
Quick Ship	-