



# LBX LED Linear Suspended

## LBX40L840-UNV

4', 4,000 Nominal Delivered Lumens, 4000K, 80 CRI, General Distribution, Oval Uplight Diffuse Lens - 137 lm/W

The LBX LED linear suspended luminaires with optional LightBalance Optics provide the versatility required for a wide range of applications. Available in 5 different configurations, LBX is easy to install and can be mounted together in runs. Where precise control is required, LightBalance Optics put the light where it's needed. Choose between narrow, medium, wide, aisle, & double asymmetric distributions.

### Product data

<b>General Information</b>		<b>Efficacy</b> 137 lm/W	
Color Temperature	4000K		
CRI	80		
Photometric Distribution Type	Direct		
Mounting	Suspended		
<b>Operating and Electrical</b>		<b>Product Data</b>	
Voltages	347/UNIV V	Order product name	LBX40L840-UNV
Luminaire Input Watts	31	EAN/UPC - Product	784197335397
<b>Mechanical and Housing</b>		Order code	912401279087
Fixture Size	48 in	Local order code	9719101
Shape	Linear	Numerator - Quantity Per Pack	1
<b>Initial Performance (IEC Compliant)</b>		Numerator - Packs per outer box	1
Luminaire Lumens	4000	Material Nr. (12NC)	912401279087
		Net Weight (Piece)	0.001 kg
		Commercial Code	LBX40L840-UNV-UD
		Catalog Number Description	4', 4,000 Nominal Delivered Lumens, 4000K, 80 CRI, General Distribution, Oval Uplight Diffuse Lens
		Quick Ship	-

