



EvoGrid Recessed LED

1x4, 4500 Nominal Delivered Lumens, 80 CRI, 4000K, Diffuse

1x4, 4500 Nominal Delivered Lumens, 80 CRI, 4000K, Diffuse – 115 lm/W

EvoGrid Recessed Architectural LED provides general lighting perfect for a wide variety of applications. Its soft opal diffuser with large luminous area minimizes apparent brightness compared to other based luminaires.

Product data

General Information	
Colour Temperature	4000K
CRI	80
Photometric Distribution Type	Direct
Mounting	Recessed
Operating and Electrical	
Voltages	120/277/347/UNIV V
Luminaire Input Watts	39
Mechanical and Housing	
Fixture Size	1 ft x 4 ft
Shape	Rectangular
Approval and Application	
DesignLights Consortium Qualified	DesignLights Consortium Qualified Product
Product List	List

Initial Performance (IEC Compliant)	
Luminaire Lumens	4500
Efficacy	115 lm/W
Product Data	
Order product name	1EVG45L840-4-D-UNV
EAN/UPC - Product	784197208622
Order code	1EVG45L840-4-D-UNV-DIM
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912401280291
Net Weight (Piece)	0.001 kg
Catalog Number	1EVG45L840-4-D-UNV-DIM
Catalog Number Description	1x4, 4500 Nominal Delivered Lumens, 80 CRI, 4000K, Diffuse