



SofTrace Recessed LED

2STG40L8TW-2-D-UNV

2x2 Tunable White, 4000 Nominal Delivered Lumens, 80 CRI,
2700-6500K, Diffuse (Smooth)

SofTrace LED brings new meaning to the concept of combining style with performance. Equipped with a fresh streamlined design and innovative technology, SofTrace provides a huge step forward for the lighting industry. The sleek profile design belies the true “horsepower under the hood”. With efficiency levels exceeding 95% and lumens per Watt as great as 87, an architectural product now delivers leading edge performance for the most environmentally conscious user.

Product data

General Information	
Color Temperature	6500K
CRI	80
Photometric Distribution Type	Direct
Mounting	Recessed
Operating and Electrical	
Voltages	120/277/347/UNIV V
Luminaire Input Watts	43
Mechanical and Housing	
Fixture Size	2 ft x 2 ft
Shape	Square
Initial Performance (IEC Compliant)	
Luminaire Lumens	4000

Product Data	
Order product name	2STG40L8TW-2-D-UNV
EAN/UPC - Product	784197327330
Order code	912401282668
Local order code	9732733
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912401282668
Net Weight (Piece)	0.001 kg
Commercial Code	2STG40L8TW-2-D-UNV-DTW
Catalog Number Description	2x2 Tunable White, 4000 Nominal Delivered Lumens, 80 CRI, 2700-6500K, Diffuse (Smooth)
Quick Ship	-