



ClearAppeal Recessed LED

2CAG49L8TW-4-DS-UNV

2x4 Tunable White, 4900 Nominal Delivered Lumens, 80 CRI, 2700-6500K, Diffuse (Smooth) - 89 lm/W

ClearAppeal Recessed Architectural LED offers smooth brightness across the face of the luminaire and provides excellent visual comfort. Its modern architectural styling complements any space.

Product data

General Information	
Color Temperature	6500K
CRI	80
Photometric Distribution Type	Direct
Mounting	Recessed
Operating and Electrical	
Voltages	120/277/347/UNIV V
Luminaire Input Watts	55
Mechanical and Housing	
Fixture Size	2 ft x 4 ft
Shape	Rectangular
Initial Performance (IEC Compliant)	
Luminaire Lumens	4900
Efficacy	89 lm/W

Product Data	
Order product name	2CAG49L8TW-4-DS-UNV
EAN/UPC - Product	784197268770
Order code	912401283320
Local order code	9726877
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912401283320
Net Weight (Piece)	0.001 kg
Commercial Code	2CAG49L8TW-4-DS-UNV-DTW
Catalog Number Description	2x4 Tunable White, 4900 Nominal Delivered Lumens, 80 CRI, 2700-6500K, Diffuse (Smooth)
Quick Ship	-