



ClearAppeal Recessed LED

2x4 Tunable White, 4900 Nominal Delivered Lumens, 80 CRI, 2700-6500K, Diffuse (Smooth)

2x4 Tunable White, 4900 Nominal Delivered Lumens, 80 CRI, 2700-6500K, Diffuse (Smooth) - 89 lm/W

ClearAppeal Recessed Architectural LED offers smooth brightness across the face of the luminaire and provides excellent visual comfort. Its modern architectural styling complements any space.

Product data

General Information		Efficacy 89 lm/W	
Colour Temperature	6500K		
CRI	80		
Photometric Distribution Type	Direct		
Mounting	Recessed		
Operating and Electrical		Product Data	
Voltages	120/277/347/UNIV V	Order product name	2CAG49L8TW-4-DS-UNV
Luminaire Input Watts	55	EAN/UPC - Product	784197268770
		Order code	2CAG49L8TW-4-DS-UNV-DTW
		Numerator - Quantity Per Pack	1
		Numerator - Packs per outer box	1
		Material Nr. (12NC)	912401283320
		Net Weight (Piece)	0.001 kg
		Catalog Number	2CAG49L8TW-4-DS-UNV-DTW
		Catalog Number Description	2x4 Tunable White, 4900 Nominal Delivered Lumens, 80 CRI, 2700-6500K, Diffuse (Smooth)
Initial Performance (IEC Compliant)			
Luminaire Lumens	4900		