



# 60 Series Exits

## 60MLA1RGA

Wet Location/Vandal Resistant LED Exit, AC Only, Single Face, Red Letters, Gray Housing and Brushed Aluminum Stencil

The 60 Line Max is designed to meet the demands of todays most extreme environments. An attractive housing constructed of durable die cast with a polycarbonate backplate and cover. Built for extreme temperatures and vandalproof applications.

### Product data

<b>General Information</b>		<b>Local order code</b> 9704818	
<b>Lamp Source Code</b>	LED	<b>Numerator - Quantity Per Pack</b>	1
<b>Mounting</b>	Wall Suspended	<b>Numerator - Packs per outer box</b>	1
<b>Operating and Electrical</b>		<b>Material Nr. (12NC)</b>	912401289536
<b>Voltages</b>	120/277 V	<b>Net Weight (Piece)</b>	0.001 kg
<b>Luminaire Input Watts</b>	4	<b>Commercial Code</b>	60MLA1RGA
<b>Product Data</b>		<b>Catalog Number Description</b>	Wet Location/Vandal Resistant LED Exit, AC Only, Single Face, Red Letters, Gray Housing and Brushed Aluminum Stencil
<b>Order product name</b>	60MLA1RGA	<b>Quick Ship</b>	-
<b>EAN/UPC - Product</b>	784197048181		
<b>Order code</b>	912401289536		