



60 Series LED Exit Sign

Wet Location/Vandal Resistant LED Exit, AC Only, Single Face, Red Letters, Gray Housing and Brushed Aluminum Stencil

Wet Location/Vandal Resistant LED Exit, AC Only, Single Face, Red Letters, Gray Housing and Brushed Aluminum Stencil

The 60 Line Max is designed to meet the demands of today's most extreme environments. An attractive housing constructed of durable die cast with a polycarbonate backplate and cover. Built for extreme temperatures and vandalproof applications.

Product data

General information	
Lamp Source Code	LED
Mounting	Wall Suspended
Number Of Pieces	1
Buy American Compliant Products	Yes

Operating and electrical	
Voltages	120/277 V
Luminaire Input Watts	4
Conduit Connection	7/8 inch knockout

Mechanical and housing	
Enclosure	Metal and Plastic

Product data	
Order product name	60MLA1RGA
EAN/UPC - Product	784197048181
Order code	60MLA1RGA
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912401289536
Net Weight (Piece)	0.001 kg
Catalog Number	60MLA1RGA
Catalog Number Description	Wet Location/Vandal Resistant LED Exit, AC Only, Single Face, Red Letters, Gray Housing and Brushed Aluminum Stencil