



# BL711 Micro Accent

BULLYTE,MICRO,12V,LED,T3 LMP,STK

Accent, Aluminum Bullyte w/ Stake, Bronze, 2W LED, 12V

The BL711 Mini-Bullyte is an excellent choice for limited space applications. It's all aluminum construction includes a fully-adjustable swivel arm with vibration-proof locking teeth. Optics include a clear tempered glass lens and requires a 20W T3 or 35W maximum MR11. Energy saving LED is available to ensure even light distribution and long life.

## Product data

General Information	
Lamp Source Code	LED
Lamp Watts	2
Number of Lamps	1
Color Temperature	3000K
CRI	80
Photometric Distribution Type	General Diffuse
Mounting	NPT/NPS
Operating and Electrical	
Voltages	12 V
Luminaire Input Watts	2
Initial Performance (IEC Compliant)	
Luminaire Lumens	200

Product Data	
Order product name	BULLYTE,MICRO,12V,LED,T3 LMP,STK
Order code	BL711-HS7LED2W
Local order code	.
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912401335009
Net Weight (Piece)	0.490 kg
Commercial Code	BL711-HS7LED2W
Catalog Number Description	Accent, Aluminum Bullyte w/ Stake, Bronze, 2W LED, 12V
Quick Ship	Service Smart (2 Days) USA