



# MUL4 Path Light

## Path Light, Aluminum w/Stake, Black, 2W LED, 12V

Path Light, Aluminum w/Stake, Black, 2W LED, 12V - 100 lm/W

The MUL path light Family of low voltage luminaires features classic mushroom styling and a graceful appearance making them suitable for most applications. Designed as a spread light, these luminaires produce a uniform light pattern with no objectionable glare. Construction choices include aluminum or Solid brass stem die-cast brass. Finishes are available in antiqued verde, bronze, sienna, speckled stone, black and natural cast bronze. Energy saving LED is available to ensure even light distribution and long life.

### Product data

General information		Initial performance (IEC compliant)	
Lamp Source Code	LED	Luminaire Lumens	200
Lamp Watts	2	Efficacy	100 lm/W
Number of Lamps	1		
Colour Temperature	3000 K	Product data	
CRI	80	Order product name	PATH,SM MUSH,12V,LED,T3 LMP,STK
Photometric Distribution Type	General Diffuse	EAN/UPC - Product	783352020468
Mounting	NPT/NPS	Order code	MUL4-AS7LED2W
Number Of Pieces	1	Numerator - Quantity Per Pack	1
		Numerator - Packs per outer box	1
Operating and electrical		Material Nr. (12NC)	912401335024
Voltages	12 V	Net Weight (Piece)	0.001 kg
Luminaire Input Watts	2	Catalog Number	MUL4-AS7LED2W
Conduit Connection	7/8 inch knockout	Catalog Number Description	Path Light, Aluminum w/Stake, Black, 2W LED, 12V
Mechanical and housing			
Enclosure	Metal and Plastic		