



CUL16 Copper Accent

ACCENT,COPPER,12V,LED,MR16 LMP,STK

Accent w/ Stake & Lamp, Copper, 7W LED, Flood

Hadco's CUL family of path lights are low voltage landscape luminaires offering a distinctive appearance to any outdoor application. The fixtures are hand crafted with a spun solid copper roof with copper stem. Optics includes a reflective white powdercoat on underside of roof with frosted tempered glass lens. Also available with a Philips MR16 LED lamp.

Product data

General Information	
Lamp Source Code	LED
Lamp Watts	2
Number of Lamps	1
Color Temperature	3000K
CRI	80
Photometric Distribution Type	Medium
Mounting	NPT/NPS
Operating and Electrical	
Voltages	12 V
Luminaire Input Watts	2
Initial Performance (IEC Compliant)	
Luminaire Lumens	200

Product Data	
Order product name	ACCENT,COPPER,12V,LED,MR16 LMP,STK
EAN/UPC - Product	046677323882
Order code	CUL16-S7LED7FLW
Local order code	-
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912401335040
Net Weight (Piece)	0.001 kg
Commercial Code	CUL16-S7LED7FLW
Catalog Number Description	Accent w/ Stake & Lamp, Copper, 7W LED, Flood
Quick Ship	-