



CUL16 Copper Accent

Accent w/ Stake & Lamp, Copper, 7W LED, Narrow Flood

Accent w/ Stake & Lamp, Copper, 7W LED, Narrow Flood

Hadco's CUL family of path lights are low voltage landscape luminaires offering a distinctive appearance to any outdoor application. The fixtures are hand crafted with a spun solid copper roof with copper stem. Optics includes a reflective white powdercoat on underside of roof with frosted tempered glass lens. Also available with a Philips MR16 LED lamp.

Product data

| General Information | |
|-------------------------------------|---------|
| Lamp Source Code | LED |
| Lamp Watts | 2 |
| Number of Lamps | 1 |
| Colour Temperature | 3000K |
| CRI | 80 |
| Photometric Distribution Type | Medium |
| Mounting | NPT/NPS |
| Operating and Electrical | |
| Voltages | 12 V |
| Luminaire Input Watts | 2 |
| Initial Performance (IEC Compliant) | |
| Luminaire Lumens | 200 |

| Product Data | |
|---------------------------------|------------------------------------------------------|
| Order product name | ACCENT,COPPER,12V,LED,MR16 LMP,STK |
| Order code | CUL16-S7LED7NFW |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 1 |
| Material Nr. (12NC) | 912401335041 |
| Net Weight (Piece) | 0.100 kg |
| Catalog Number | CUL16-S7LED7NFW |
| Catalog Number Description | Accent w/ Stake & Lamp, Copper, 7W LED, Narrow Flood |