



CUL14 Path Light

PATH,COPPER,12V,LED,T3 LMP,STK

Path Light, w/ Stake, Copper, 2W LED, 3000K, 12V

Hadco's CUL family of path lights are low voltage landscape luminaires offering a distinctive appearance to any outdoor application. The fixtures are hand crafted with a spun solid copper roof with copper stem. Optics includes a reflective white powdercoat on underside of roof with frosted tempered glass lens. Sources include standard low voltage lamps and LED that offers 50,000 hours of operating life, has a CCT of 3,000K or 4,000K and a CRI of 80.

Product data

| General Information | |
|-------------------------------------|-----------------|
| Lamp Source Code | LED |
| Lamp Watts | 2 |
| Number of Lamps | 1 |
| Color Temperature | 3000K |
| CRI | 80 |
| Photometric Distribution Type | General Diffuse |
| Mounting | NPT/NPS |
| Operating and Electrical | |
| Voltages | 12 V |
| Luminaire Input Watts | 2 |
| Initial Performance (IEC Compliant) | |
| Luminaire Lumens | 200 |

| Product Data | |
|---------------------------------|--|
| Order product name | PATH,COPPER,12V,LED,T3 LMP,STK |
| Order code | CUL14-S7LED2W |
| Local order code | . |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 1 |
| Material Nr. (12NC) | 912401335076 |
| Net Weight (Piece) | 0.100 kg |
| Commercial Code | CUL14-S7LED2W |
| Catalog Number Description | Path Light, w/ Stake, Copper, 2W LED, 3000K, 12V |
| Quick Ship | - |