



# MileWide² Pole

## YHP435 PLT-FLG CUR 6000 RAL 60/48

Pole with flange, 6.0 m, 80 mm, RAL color

Many municipal authorities are embracing the benefits of contemporary outdoor lighting. These include a more attractive urban environment and increased comfort, safety and security for the public. Not to mention the positive impact on environmental protection and city branding. Together with Holscher Design, Philips has developed MileWide², the successor to the highly popular MileWide family. Featuring a range of dedicated masts and brackets, the pure, clean design of MileWide² integrates perfectly with today's and tomorrow's cityscape. With its high-quality finish and high level of lighting performance, MileWide² is suitable for a wide range of applications, ranging from traffic roads to city centers. Multi-layer optics provide a uniform light distribution and reduced glare, enabling direct replacement of HID solutions without compromising on spacing, mounting height or light quality.

### Product data

General Information	
Pole type	Pole with flange
Pole color	RAL color
Value ladder	Specification
Mechanical and Housing	
Fixation diameter	Mounting device diameter 60 mm and 48 mm
Pole top diameter	80 mm
Pole height	6.0 m
Product Data	
Order product name	YHP435 PLT-FLG CUR 6000 RAL 60/48

Full product name	YHP435 PLT-FLG CUR 6000 RAL 60/48
Full product code	871869938167700
Order code	912401451658
Material Nr. (12NC)	912401451658
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699381677
Numerator - Packs per outer box	1
EAN/UPC - Case	8718699381677

## MileWide<sup>2</sup> Pole

### Dimensional drawing

