



MileWide² Pole

YHP435 PLS-EMB CUR 6000 RAL 60

Pole for embedded installation, 6.0 m, 80 mm, RAL color

Many municipal authorities are embracing the benefits of contemporary outdoor lighting. These include a more attractive urban environment and increased comfort, safety and security for the public. Not to mention the positive impact on environmental protection and city branding. Together with Holscher Design, Philips has developed MileWide², the successor to the highly popular MileWide family. Featuring a range of dedicated masts and brackets, the pure, clean design of MileWide² integrates perfectly with today's and tomorrow's cityscape. With its high-quality finish and high level of lighting performance, MileWide² is suitable for a wide range of applications, ranging from traffic roads to city centers. Multi-layer optics provide a uniform light distribution and reduced glare, enabling direct replacement of HID solutions without compromising on spacing, mounting height or light quality.

Product data

General Information		Full product name	
Pole type	Pole for embedded installation	Full product code	YHP435 PLS-EMB CUR 6000 RAL 60
Pole color	RAL color	Order code	871869938168400
Value ladder	Specification	Material Nr. (12NC)	912401451659
Mechanical and Housing		Numerator - Quantity Per Pack	912401451659
Fixation diameter	Mounting device diameter 60 mm	EAN/UPC - Product/Case	1
Pole top diameter	80 mm	Numerator - Packs per outer box	8718699381684
Pole height	6.0 m	EAN/UPC - Case	1
Product Data		8718699381684	
Order product name	YHP435 PLS-EMB CUR 6000 RAL 60		

MileWide² Pole

Dimensional drawing

