



MileWide² Pole

YHP435 PLS-EMB CUR 4000 RAL 48

Pole for embedded installation, 4.0 m, 70 mm, RAL color

Many municipal authorities are embracing the benefits of contemporary outdoor lighting. These include a more attractive urban environment and increased comfort, safety and security for the public. Not to mention the positive impact on environmental protection and city branding. Together with Holscher Design, Philips has developed MileWide², the successor to the highly popular MileWide family. Featuring a range of dedicated masts and brackets, the pure, clean design of MileWide² integrates perfectly with today's and tomorrow's cityscape. With its high-quality finish and high level of lighting performance, MileWide² is suitable for a wide range of applications, ranging from traffic roads to city centers. Multi-layer optics provide a uniform light distribution and reduced glare, enabling direct replacement of HID solutions without compromising on spacing, mounting height or light quality.

Product data

| General Information | | Full product name | |
|------------------------|--------------------------------|---------------------------------|--------------------------------|
| Pole type | Pole for embedded installation | Full product code | YHP435 PLS-EMB CUR 4000 RAL 48 |
| Pole color | RAL color | Order code | 871869938171400 |
| Value ladder | Specification | Material Nr. (12NC) | 912401451662 |
| Mechanical and Housing | | Numerator - Quantity Per Pack | 1 |
| Fixation diameter | Mounting device diameter 48 mm | EAN/UPC - Product/Case | 8718699381714 |
| Pole top diameter | 70 mm | Numerator - Packs per outer box | 1 |
| Pole height | 4.0 m | EAN/UPC - Case | 8718699381714 |
| Product Data | | | |
| Order product name | YHP435 PLS-EMB CUR 4000 RAL 48 | | |

Dimensional drawing

