



FluxPanel LED

1x4, 3800 Nominal Delivered Lumens, 80 CRI, 4000K, Diffuse

1x4, 3800 Nominal Delivered Lumens, 80 CRI, 4000K, Diffuse – 107 lm/W

Day-Brite / CFI FluxPanel LED recessed is a highly versatile luminaire designed to provide smooth lighting gradient on the lens surface and ease of installation. Available for use in recessed, suspended, and surface mount orientation, FluxPanel is ideal for general lighting applications such as open office, schools, healthcare, and retail.

Product data

General Information	
Colour Temperature	4000K
CRI	80
Mounting	Recessed Surface Suspended
Operating and Electrical	
Voltages	120/277/347/UNIV V
Luminaire Input Watts	33
Mechanical and Housing	
Fixture Size	1 ft x 4 ft
Shape	Rectangular
Approval and Application	
DesignLights Consortium Qualified	DesignLights Consortium Qualified Product
Product List	List

Initial Performance (IEC Compliant)	
Luminaire Lumens	3800
Efficacy	107 lm/W
Product Data	
Order product name	1FXP38B840-4-DS-UNV (2 PACKS ONLY)
EAN/UPC - Product	784197381349
Order code	1FXP38B840-4-DS-UNV-DIM
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2
Material Nr. (12NC)	912401454794
Net Weight (Piece)	3.820 kg
Catalog Number	1FXP38B840-4-DS-UNV-DIM
Catalog Number Description	1x4, 3800 Nominal Delivered Lumens, 80 CRI, 4000K, Diffuse