



# FluxPanel LED

2x2, 3800 Nominal Delivered Lumens, 80 CRI, 3500K, Diffuse

2x2, 3800 Nominal Delivered Lumens, 80 CRI, 3500K, Diffuse – 110 lm/W

Day-Brite / CFI FluxPanel LED recessed is a highly versatile luminaire designed to provide smooth lighting gradient on the lens surface and ease of installation. Available for use in recessed, suspended, and surface mount orientation, FluxPanel is ideal for general lighting applications such as open office, schools, healthcare, and retail.

## Product data

General Information	
Colour Temperature	3500K
CRI	80
Mounting	Recessed Surface Suspended
Operating and Electrical	
Voltages	120/277/347/UNIV V
Luminaire Input Watts	33
Mechanical and Housing	
Fixture Size	2 ft x 2 ft
Shape	Square
Approval and Application	
DesignLights Consortium Qualified	DesignLights Consortium Qualified Product
Product List	List

Initial Performance (IEC Compliant)	
Luminaire Lumens	3800
Efficacy	110 lm/W
Product Data	
Order product name	2FXP38B835-2-DS-UNV (2 PACKS ONLY)
EAN/UPC - Product	784197381363
Order code	2FXP38B835-2-DS-UNV-DIM
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2
Material Nr. (12NC)	912401454796
Net Weight (Piece)	3.600 kg
Catalog Number	2FXP38B835-2-DS-UNV-DIM
Catalog Number Description	2x2, 3800 Nominal Delivered Lumens, 80 CRI, 3500K, Diffuse