



# SofTrace Recessed LED

## 2STG35B840-2-D-UNV

2x2, 3500 Nominal Delivered Lumens, 80 CRI, 4000K, Diffuse-Smooth - 107 lm/W

SofTrace LED brings new meaning to the concept of combining style with performance. Equipped with a fresh streamlined design and innovative technology, SofTrace provides a huge step forward for the lighting industry. The sleek profile design belies the true "horsepower under the hood". With efficiency levels exceeding 95% and lumens per Watt as great as 87, an architectural product now delivers leading edge performance for the most environmentally conscious user.

### Product data

General Information		Initial Performance (IEC Compliant)	
Color Temperature	4000K	Luminaire Lumens	3500
CRI	80	Efficacy	107 lm/W
Photometric Distribution Type	Direct		
Mounting	Recessed		
Operating and Electrical		Product Data	
Voltages	120/277/347 V	Order product name	2STG35B840-2-D-UNV
Luminaire Input Watts	33	EAN/UPC - Product	784197610180
		Order code	912401456761
		Local order code	9761018
		Numerator - Quantity Per Pack	1
		Numerator - Packs per outer box	1
		Material Nr. (12NC)	912401456761
		Net Weight (Piece)	0.001 kg
		Commercial Code	2STG35B835-2-D-UNV-DIM
		Catalog Number Description	2x2, 3500 Nominal Delivered Lumens, 80 CRI, 4000K, Diffuse-Smooth
		Quick Ship	-
Approval and Application			
DesignLights Consortium Qualified Product List		DesignLights Consortium Qualified Product List	

