



SofTrace Recessed LED

2x4, 4100 Nominal Delivered Lumens, 80 CRI, 4000K, Diffuse-Smooth

2x4, 4100 Nominal Delivered Lumens, 80 CRI, 4000K, Diffuse-Smooth - 127 lm/W

SofTrace LED brings new meaning to the concept of combining style with performance. Equipped with a fresh streamlined design and innovative technology, SofTrace provides a huge step forward for the lighting industry. The sleek profile design belies the true “horsepower under the hood”. With efficiency levels exceeding 95% and lumens per Watt as great as 87, an architectural product now delivers leading edge performance for the most environmentally conscious user.

Product data

General Information		Shape	
Colour Temperature	4000K	Rectangular	
CRI	80	Approval and Application	
Photometric Distribution Type	Direct	DesignLights Consortium Qualified	DesignLights Consortium Qualified Product
Mounting	Recessed	Product List	List
Operating and Electrical		Initial Performance (IEC Compliant)	
Voltages	120/277/347 V	Luminaire Lumens	4100
Luminaire Input Watts	33	Efficacy	127 lm/W
Mechanical and Housing		Product Data	
Fixture Size	2 ft x 4 ft	Order product name	2STG41B840-4-D-UNV
		EAN/UPC - Product	784197610272

SofTrace Recessed LED

Order code	2STG41B840-4-D-UNV-DIM
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912401456763
Net Weight (Piece)	0.001 kg

Catalog Number	2STG41B840-4-D-UNV-DIM
Catalog Number Description	2x4, 4100 Nominal Delivered Lumens, 80 CRI, 4000K, Diffuse-Smooth

