



ClearAppeal Recessed LED

2x4, 4000 Nominal Delivered Lumens, 80 CRI, 4000K, Diffuse (Smooth), Dimming Driver

2x4, 4000 Nominal Delivered Lumens, 80 CRI, 4000K, Diffuse (Smooth), Dimming Driver – 121 lm/W

ClearAppeal Recessed Architectural LED offers smooth brightness across the face of the luminaire and provides excellent visual comfort. Its modern architectural styling complements any space.

Product data

General Information	
Colour Temperature	4000K
CRI	80
Photometric Distribution Type	Direct
Mounting	Recessed
Operating and Electrical	
Voltages	347/UNIV V
Luminaire Input Watts	32
Mechanical and Housing	
Fixture Size	2 ft x 4 ft
Shape	Rectangular

Approval and Application	
DesignLights Consortium Qualified	DesignLights Consortium Qualified Product
Product List	List

Initial Performance (IEC Compliant)	
Luminaire Lumens	4000
Efficacy	121 lm/W

Product Data	
Order product name	2CAG40B840-4-DS-UNV
EAN/UPC - Product	784197610449
Order code	2CAG40B840-4-DS-UNV-DIM
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912401456767
Net Weight (Piece)	0.001 kg

ClearAppeal Recessed LED

Catalog Number	2CAG40B840-4-DS-UNV-DIM
Catalog Number Description	2x4, 4000 Nominal Delivered Lumens, 80 CRI, 4000K, Diffuse (Smooth), Dimming Driver

