



ClearAppeal Recessed LED

2x2, 3300 Nominal Delivered Lumens, 80 CRI, 4000K, Diffuse (Smooth), Dimming Driver

2x2, 3300 Nominal Delivered Lumens, 80 CRI, 4000K, Diffuse (Smooth), Dimming Driver – 100 lm/W

ClearAppeal Recessed Architectural LED offers smooth brightness across the face of the luminaire and provides excellent visual comfort. Its modern architectural styling complements any space.

Product data

General Information		Efficacy	
Colour Temperature	4000K	100 lm/W	
CRI	80		
Photometric Distribution Type	Direct		
Mounting	Recessed		
Operating and Electrical		Product Data	
Voltages	347/UNIV V	Order product name	2CAG33B840-2-DS-UNV
Luminaire Input Watts	34	EAN/UPC - Product	784197610623
Mechanical and Housing		Order code	2CAG33B840-2-DS-UNV-DIM
Fixture Size	2 ft x 2 ft	Numerator - Quantity Per Pack	1
Shape	Square	Numerator - Packs per outer box	1
Initial Performance (IEC Compliant)		Material Nr. (12NC)	912401456773
Luminaire Lumens	3300	Net Weight (Piece)	0.001 kg
		Catalog Number	2CAG33B840-2-DS-UNV-DIM
		Catalog Number Description	2x2, 3300 Nominal Delivered Lumens, 80 CRI, 4000K, Diffuse (Smooth), Dimming Driver