



WP Wall Pack Large LED

WP-LED-72L-530-NW-UNV-BZ

WP Wallpack, 72 LEDs, 530mA, 4000K - 57 lm/W

The Stonco LED wallpack large WP offers maximum light output for general purpose area and security lighting through a classic glass refractor design. Now available with enhanced the Philips LEDGINE platform, WP LED provides improved energy savings compared to the former LED design. This versatile luminaire is ideal to match same as existing or retrofit HID legacy designs.

Product data

| General Information | |
|-------------------------------------|--------------------------------|
| Lamp Source Code | LED |
| Lamp Watts | 65 |
| Color Temperature | 4000K |
| CRI | 70 |
| Mounting | Wall |
| Operating and Electrical | |
| Voltages | 120/208/240/277/347/480/UNIV V |
| Luminaire Input Watts | 65 |
| Initial Performance (IEC Compliant) | |
| Luminaire Lumens | 6726 |
| Efficacy | 57 lm/W |

| Product Data | |
|---------------------------------|------------------------------------|
| Order product name | WP-LED-72L-530-NW-UNV-BZ |
| Order code | WP-LED-72L-530-NW-UNV-BZ |
| Local order code | . |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 1 |
| Material Nr. (12NC) | 912401463592 |
| Net Weight (Piece) | 0.001 kg |
| Commercial Code | WP-LED-72L-530-NW-UNV-BZ |
| Catalog Number Description | WP Wallpack, 72 LEDs, 530mA, 4000K |
| Quick Ship | Service Smart (2 Days) USA |