



WPM Wall Pack Medium LED

WPM-LED-36L-530-NW-UNV-BZ

WPM LED Wallpack, 36LEDs, 530mA, 4000K

The Stonco LED wallpack medium WPM offers maximum light output for general purpose area and security lighting through a classic glass refractor design. Now available with enhanced Philips LED platforms, WPM LED provides improved energy savings compared to the former LED design. This versatile luminaire is ideal to match same as existing or retrofit HID legacy designs

Product data

General Information	
Lamp Source Code	LED
Lamp Watts	33
Color Temperature	4000K
CRI	70
Mounting	Wall
Operating and Electrical	
Voltages	120/208/240/277 V
Luminaire Input Watts	33
Initial Performance (IEC Compliant)	
Luminaire Lumens	3052

Product Data	
Order product name	WPM-LED-36L-530-NW-UNV-BZ
Order code	WPM-LED-36L-530-NW-UNV-BZ
Local order code	.
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912401465112
Net Weight (Piece)	0.100 kg
Commercial Code	WPM-LED-36L-530-NW-UNV-BZ
Catalog Number Description	WPM LED Wallpack, 36LEDs, 530mA, 4000K
Quick Ship	Service Smart (2 Days) USA