



# LED General Purpose Floods FL

LED, 80W, 4000K, Wide Flood Optics, Textured Dark Bronze

LED, 80W, 4000K, Wide Flood Optics, Textured Dark Bronze – 113 lm/W

The General Purpose LED Floodlights offer energy saving LED technology for long life and reduced maintenance. Versatile and stylish with five different sizes to choose from provides application flexibility for ground mount, wall mount, or pole mount installations. Ideal for sign lighting, building facades, security lighting, and general purpose floodlighting applications.

## Product data

General information		Mechanical and housing	
Lamp Source Code	LED	Shape	Rectangular
Colour Temperature	4000 K	Material	Aluminum
CRI	80	Enclosure	Metal and Plastic
Photometric Distribution Type	NEMA 7H x 6V	Approval and application	
Mounting	Surface Ground / Floor Wall	Safety Listing	UL
Number Of Pieces	1	Energy Certifications	DLC Standard cULus
Grade	Value Grade	IP Rating	IP66 [ Dust penetration-protected, jet-proof]
Operating and electrical		Initial performance (IEC compliant)	
Voltages	120/208/240/277 V	Luminaire Lumens	8856
Luminaire Input Watts	79	Efficacy	113 lm/W
Conduit Connection	7/8 inch knockout		

LED General Purpose Floods FL

Application conditions	
Ambient temperature range	-40 °C to 40 °C
Max Ambient Temp	40 °C
Min Ambient Temp	-40 °C
Min Ambient Temp-DUP(do not use)	-40 °C
Product data	
Order product name	FL80-NW-G1-T-FL-8-BZ
EAN/UPC - Product	783352024176
Order code	FL80-NW-G1-T-FL-8-BZ

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912401467973
Net Weight (Piece)	7.000 kg
Catalog Number	FL80-NW-G1-T-FL-8-BZ
Catalog Number Description	LED, 80W, 4000K, Wide Flood Optics, Textured Dark Bronze

