



# PlainView, recessed

## RC140B LED38S/840 PSD PCV PI5 L1150

840 neutral white, Power supply unit with DALI interface, Push-in connector 5-pole

Light line solutions are always in fashion. therefore we know that delivering innovation in this field is crucial. PlainView is a modern looking, neat luminaire offering comfortable, good quality lighting and can also work as a design element. The luminaires offer high quality specifications and flexibility with different options for lumen packages. Thanks to these features and benefits, PlainView delivers ideal lighting in the non-working areas of professional spaces such as offices, educational institutes, and also the welcoming areas and entrances of retail spaces.

### Product data

General Information	
Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.
Service tag	Yes
Lighting Technology	LED
Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes

ENEC mark	-
Warranty period	5 years
EU RoHS compliant	Yes
Value ladder	Performance
Light Technical	
Luminous Flux	3,800 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	90 lm/W
Color rendering index (CRI)	≥80
Light source color	840 neutral white
Optic type	-
Luminaire light beam spread	100°
Unified glare rating CEN	28

PlainView, recessed

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	22 A
Inrush time	275 ms
Power Consumption	40 W
Power Factor (Fraction)	0.9
Connection	Push-in connector 5-pole
Cable	-
Number of products on MCB of 16 A type B	24

Temperature	
Ambient temperature range	+10 to +40 °C

Controls and Dimming	
Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

Mechanical and Housing	
Housing Material	Aluminum
Reflector material	-
Optic material	-
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	White
Optical cover finish	Opal
Overall length	1,150 mm
Overall width	74 mm

Overall height	82 mm
Dimensions (Height x Width x Depth)	82 x 74 x 1150 mm


Approval and Application	
Ingress protection code	IP40 [Wire-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-10%

Application Conditions	
Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Yes

Product Data	
Order product name	RC140B LED38S/840 PSD PCV PI5 L1150
Full product name	RC140B LED38S/840 PSD PCV PI5 L1150
Full product code	871869938023699
Order code	912401483009
Material Nr. (12NC)	912401483009
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699380236
Numerator - Packs per outer box	4
EAN/UPC - Case	8718699380311

Dimensional drawing



PlainView, recessed

