



CoreLine panel

RC132V LED36S/840 W30L120 IA1 OC

CoreLine panel, 34 W, 1200x300 mm, 3600 lm, 4000 K,
Wireless, Interact Ready, UGR19

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Panel range of LED products can be used to replace functional luminaires in general lighting applications. Both Non-Office Compliant (NOC) version and Office Compliant version (OC) are now available. The process of selecting, installing and maintaining is so easy – it's a simple switch.

Product data

General Information			
Light source replaceable	No	Warranty period	5 years
Number of gear units	1 unit	Flammability mark	For mounting on normally flammable surfaces
Driver included	Yes	ENEC mark	ENEC mark
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	Glow-wire test	Temperature 650 °C, duration 30 s
Service tag	Yes	EU RoHS compliant	Yes
Connectivity	Interact Ready	Light Technical	
Lighting Technology	LED	Luminous Flux	3,600 lm
Value ladder	Performance	Correlated Color Temperature (Nom)	4000 K
Embedded control	Interact SNS210 sensor	Luminous Efficacy (rated) (Nom)	100 lm/W
CE mark	Yes	Color rendering index (CRI)	≥80
		Beam angle of light source	120 degree(s)
		Light source color	840 neutral white
		Optic type	-
		Luminaire light beam spread	90°

CoreLine panel

Unified glare rating CEN	19
--------------------------	----

Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Average CLO power consumption	35 W
Inrush current	8 A
Inrush time	0.25 ms
Power Consumption	34 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	24

Temperature	
Ambient temperature range	+10 to +40 °C

Controls and Dimming	
Dimmable	Yes
Driver/power unit/transformer	Power supply unit regulating
Control interface	Wireless
Constant light output	No

Mechanical and Housing	
Housing Material	Aluminum
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover material	Polymethyl methacrylate
Fixation material	-
Housing Color	White
Optical cover finish	Opal
Overall length	1,197 mm
Overall width	297 mm
Overall height	42 mm
Dimensions (Height x Width x Depth)	42 x 297 x 1197 mm

Approval and Application	
Ingress protection code	IP20/44 [Finger-protected; wire-protected, splash-proof]
Mech. impact protection code	IK03 [0.3 J]
Sustainability rating	-
Protection class IEC	Safety class I


Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)	
Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L75

Application Conditions	
Performance ambient temperature Tq	25 °C
Maximum dim level	10%
Suitable for random switching	Yes

Product Data	
Order product name	RC132V LED36S/840 W30L120 IA1 OC
Full product name	RC132V LED36S/840 W30L120 IA1 OC
Full product code	871869938523100
Order code	38523100
Material Nr. (12NC)	912401483130
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699385231
Numerator - Packs per outer box	1
EAN/UPC - Case	8718699385231

Dimensional drawing



CoreLine panel

