



# CoreLine Wall-mounted

## WL131V LED20S/830 PSR MDU WH

CoreLine Wall-mounted, 25 W, D350 mm, 2000 lm, 3000 K, Sensor-based dim, IP65

CoreLine Wall-mounted is a circular-shaped surface-mounted luminaire that is easy to apply in circulation areas such as hallways and staircases. The modern unobtrusive design, in combination with its homogeneous light distribution it delivers, ensures that this luminaire blends into most building architectures. With the push-in connectors, installation is fast and straightforward

### Product data

General Information			
Lamp family code	LED20 [LED Module 2000 lm]	CE mark	Yes
Light source replaceable	No	Warranty period	5 years
Number of gear units	Unit	Flammability mark	-
Driver included	Yes	ENEC mark	ENEC mark
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value.	Glow-wire test	Temperature 650 °C, duration 30 s
Lighting Technology	LED	EU RoHS compliant	Yes
Value ladder	Performance	Light Technical	
Embedded control	Movement detection unit	Luminous Flux	2,000 lm
		Correlated Colour Temperature	3000 K
		Luminous efficacy (rated) (nom.)	80 lm/W
		Colour rendering index (CRI)	80
		Beam angle of light source	120 degree(s)
		Light source colour	830 warm white
		Optic type	Opal prismatic reflector
		Optical cover type	Opal bowl with painted cover

## CoreLine Wall-mounted

Luminaire light beam spread	120°
-----------------------------	------

### Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	NA W
Average CLO power consumption	NA W
End CLO power consumption	NA W
Inrush current	27 A
Inrush time	265 ms
Power Consumption	25 W
Power Factor (Fraction)	0.8
Connection	Push-in connector 6-pole
Cable	-
Number of products on MCB of 16 A type B	18

### Temperature

Ambient temperature range	-20 to +40 °C
---------------------------	---------------

### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit regulating
Control interface	Sensor-based dim
Constant light output	No

### Mechanical and Housing

Housing material	Polyamide
Reflector material	-
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	-
Housing Colour	White
Optical cover/lens finish	Opal
Overall length	350 mm
Overall width	350 mm
Overall height	95 mm

Overall diameter	350 mm
Dimensions (height x width x depth)	95 x 350 x 350 mm

### Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Protection class IEC	Safety class II

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.44, 0.41) SDCM<3
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)

Driver failure rate at 5,000 hours	0.7 %
Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* L70 50,000 h	


### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	10%
Suitable for random switching	Yes

### Product Data

Order product name	WL131V LED20S/830 PSR MDU WH
Full product name	WL131V LED20S/830 PSR MDU WH
Full EOC	871869938788499
Order code	38788499
Material no. (12 NC)	912401483192
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718699387884
Numerator – packs per outer box	6
EAN/UPC - Case	8718699388065

## Dimensional drawing



## CoreLine Wall-mounted

