



# CoreLine Wall-mounted

## WL131V LED12S/830 PSED WH

CoreLine Wall-mounted, 13 W, D350 mm, 1200 lm, 3000 K, DALI, IP65, EL-DC

CoreLine Wall-mounted is a circular-shaped surface-mounted luminaire that is easy to apply in circulation areas such as hallways and staircases. The modern unobtrusive design, in combination with its homogeneous light distribution it delivers, ensures that this luminaire blends into most building architectures. With the push-in connectors, installation is fast and straightforward

### Product data

General Information			
Lamp family code	LED12 [LED Module 1200 lm]	Warranty period	5 years
Light source replaceable	No	Flammability mark	-
Number of gear units	Unit	ENEC mark	ENEC mark
Driver included	Yes	Glow-wire test	Temperature 650 °C, duration 30 s
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value.	EU RoHS compliant	Yes
Lighting Technology		Light Technical	
Lighting Technology	LED	Luminous Flux	1,200 lm
Value ladder	Performance	Correlated Colour Temperature	3000 K
CE mark	Yes	Luminous efficacy (rated) (nom.)	90 lm/W
		Colour rendering index (CRI)	80
		Beam angle of light source	120 degree(s)
		Light source colour	830 warm white
		Optic type	Opal prismatic reflector
		Optical cover type	Opal bowl with painted cover

## CoreLine Wall-mounted

Luminaire light beam spread	120°
-----------------------------	------

### Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	NA W
Average CLO power consumption	NA W
End CLO power consumption	NA W
Inrush current	22 A
Inrush time	290 ms
Power Consumption	13 W
Power Factor (Fraction)	0.9
Connection	Push-in connector 6-pole
Cable	-
Number of products on MCB of 16 A type B	20

### Temperature

Ambient temperature range	-20 to +40 °C
---------------------------	---------------


### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

### Mechanical and Housing

Housing material	Polyamide
Reflector material	-
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	-
Housing Colour	White
Optical cover/lens finish	Opal
Overall length	350 mm
Overall width	350 mm
Overall height	95 mm

## Dimensional drawing



Overall diameter	350 mm
Dimensions (height x width x depth)	95 x 350 x 350 mm

### Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Protection class IEC	Safety class II

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.44, 0.41) SDCM<3
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)

Driver failure rate at 5,000 hours	0.7 %
Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L70

### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	10%
Suitable for random switching	Yes

### Product Data

Order product name	WL131V LED12S/830 PSED WH
Full product name	WL131V LED12S/830 PSED WH
Full EOC	871869938792199
Order code	38792199
Material no. (12 NC)	912401483196
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718699387921
Numerator – packs per outer box	6
EAN/UPC - Case	8718699388102

## CoreLine Wall-mounted

