



GreenSpace

DN462B LED11S/830 PSD-VLC-E C PCC WH

GreenSpace, 9 W, 1030 lm, 3000 K, DALI, Clear

GreenSpace is a perfect solution where customers want to strike the ideal balance between their initial investment and the cost of the installation during its lifetime while they are covering multiple applications. GreenSpace features the latest LED technology which enables extremely low power consumption. With its perfect fit you'll get the LED downlight that always fits and looks perfect at the same time. This perfect fit is available for cut out sizes from 150 to 280 mm. GreenSpace is designed for Circular Economy with optimized performance, extended lifetime through upgradability and integration options, ease of customization, recycling and disassembly. Housing and rim are made from production waste of polycarbonate sheets that are retrieved from swimming pools, car ports and illuminated advertising. And the product's long lifetime makes it a true 'fit and forget' solution.

Product data

General Information			
Lamp family code	LED11S [LED Module, system flux 1100 lm]	Service tag	Yes
Cap-Base	- [-]	Product family code	DN462B [150mm, IP54 (PCO UGR27)]
Light source replaceable	No	Lighting Technology	LED
Number of gear units	1 unit	Value ladder	Specification
Gear	-	CE mark	Yes
Driver included	Yes	Warranty period	5 years
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	Flammability mark	-
		ENEC mark	ENEC mark
		Glow-wire test	Temperature 750 °C, duration 5 s
		EU RoHS compliant	Yes
Light Technical			
Luminous Flux	1,030 lm		
Correlated Color Temperature (Nom)	3000 K		

Luminous Efficacy (rated) (Nom)	114 lm/W
Color rendering index (CRI)	>80
Number of light sources	1
Beam angle of light source	- degree(s)
Light source color	830 warm white
Optic type	High-gloss mirror
Luminaire light beam spread	120°
Unified glare rating CEN	22

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	- W
Average CLO power consumption	- W W
Inrush current	20.4 A
Inrush time	0.195 ms
Power Consumption	9 W
Power Factor (Fraction)	0.9
Connection	Feed-through connector 5-pole
Cable	-
Number of products on MCB of 16 A type B	24

Temperature

Ambient temperature range	-15 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface, DC compatible, external
Control interface	DALI
Constant light output	No

Mechanical and Housing

Housing Material	Polycarbonate
Reflector material	Polycarbonate aluminum coated
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	-
Housing Color	White RAL 9003
Optical cover finish	Clear

Overall height	77 mm
Overall diameter	166 mm

Approval and Application

Ingress protection code	IP54 [Dust accumulation-protected, splash-proof]
Mech. impact protection code	IK06 [1 J]
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.44, 0.40) SDCM<3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	1 %
Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* L90	
50000 h	
Lumen maintenance at median useful life* L80	
100000 h	

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Yes

Product Data

Order product name	DN462B LED11S/830 PSD-VLC-E C PCC WH
Full product name	DN462B LED11S/830 PSD-VLC-E C PCC WH
Full product code	871869938464700
Order code	912500100064
Material Nr. (12NC)	912500100064
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699384647
Numerator - Packs per outer box	1
EAN/UPC - Case	8718699384647

Dimensional drawing

