



# HID-HeavyDuty BHL for HPL/HPI

## BHL 125 L40 230V 50Hz HD1-118


Encapsulated electromagnetic copper/iron ballasts for HPL, HPI (Plus) and SON-H lamps

### Product data

<b>Operating and Electrical</b>		<b>Full product name</b>	BHL 125 L40 230V 50Hz HD1-118
Input Voltage	230 V	Full product code	871150091514631
Line Frequency	50 Hz	Order code	913602950426
Input Frequency	50 Hz	Material Nr. (12NC)	913602950426
<b>Wiring</b>		Numerator - Quantity Per Pack	1
Connector Type	Screw	EAN/UPC - Product/Case	8711500915146
<b>Approval and Application</b>		Numerator - Packs per outer box	6
Approval Marks	CE marking ENEC certificate	EAN/UPC - Case	8711500061744
<b>Product Data</b>			
Order product name	BHL 125 L40 230V 50Hz HD1-118		

# HID-HeavyDuty BHL for HPL/HPI

## Dimensional drawing



Product	D1	C1	A1	A2	B1
BHL 125 L40 230V 50Hz HD1-118	6.2 mm	53.0 mm	118.0 mm	103.0 mm	65.0 mm

