



Image
not
available

Pole gear trays EGS350

EGS350 HPI-T250W LV

EGS350, HPI-T High Wattage, 250 W

A range of prewired foot pole gear trays is available for Road Lighting luminaires. A gear tray consists of a metal tray on which electrical components (capacitors, ballast, ignitor), wiring and terminal blocks are mounted. These gear trays are normally used in combination with Road luminaires, which cannot integrate electrical components because of lack of space or because of high temperatures.

Product data

General Information		Protection class IEC	
Lamp family code	HPI-T [HPI-T High Wattage]		Safety class I
Product family code	EGS350 [EGS350]	Product Data	
CE mark	Yes	Order product name	EGS350 HPI-T250W LV
ENEC mark	ENEC mark	Full product name	EGS350 HPI-T250W LV
		Full product code	871155916804300
		Order code	913603160318
		Material Nr. (12NC)	913603160318
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8711559168043
		Numerator - Packs per outer box	1
		EAN/UPC - Case	8711559168043
Light Technical			
Number of light sources	1		
Operating and Electrical			
Input Voltage	230 V		
Power Consumption	250 W		
Approval and Application			
Ingress protection code	IP21 [Finger-protected, drip-proof]		

Pole gear trays EGS350

Dimensional drawing

Image
not
available

