



Image  
not  
available

# Pole gear trays EGS350

## EGS350 HPI-T400W LV

EGS350, HPI-T High Wattage, 400 W

A range of prewired foot pole gear trays is available for Road Lighting luminaires. A gear tray consists of a metal tray on which electrical components (capacitors, ballast, ignitor), wiring and terminal blocks are mounted. These gear trays are normally used in combination with Road luminaires, which cannot integrate electrical components because of lack of space or because of high temperatures.

### Product data

General Information	
Lamp family code	HPI-T [HPI-T High Wattage]
Product family code	EGS350 [EGS350]
CE mark	Yes
ENEC mark	ENEC mark
Light Technical	
Number of light sources	1
Operating and Electrical	
Input Voltage	230 V
Power Consumption	400 W
Approval and Application	
Ingress protection code	IP21 [Finger-protected, drip-proof]

Protection class IEC	Safety class I
Product Data	
Order product name	EGS350 HPI-T400W LV
Full product name	EGS350 HPI-T400W LV
Full product code	871155916808100
Order code	913604140418
Material Nr. (12NC)	913604140418
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559168081
Numerator - Packs per outer box	1
EAN/UPC - Case	8711559168081

## Pole gear trays EGS350

### Dimensional drawing

Image  
not  
available

